

The All-rounder series

MAGDOS solenoid diaphragm dosing pumps 0.36 – 15 l/h, up to 16 bar



Reliable dosing of chemicals

The solenoid-driven diaphragm dosing pump MAGDOS stands for dosing without compromises. Thanks to a number of the various pump types there is the right individual solution for every application, also for the highest demands. All pumps of the MAGDOS L series are certified according to UL and CSA.

The power ranges cover from 0.36 to 15 l/h with back pressures up to 16 bar. Double-ball valves ensure exact dosing. The dosing power can be adapted by varying the stroke frequency manually, via an external control contact or using a 0/4 – 20 mA signal.

Several different materials and connections are available for discharge and suction side, depending on the specific applications. Accessory sets consisting of a hose, injection nozzle and suction line are available to enable optimal results and quick installation.

Easy handling

Thanks to the sturdy, maintenance-free solenoid drive, the media being supplied (acids, alkalis, coagulants and flocculants, for example) are reliably and accurately dosed.

The MAGDOS does not just impress with their elegant design. The MAGDOS is available with a graphic display and multi-language menu. You can read the status of the MAGDOS from the backlight of the display. This, together with the operation via the integrated keyboard, ensures easy handling.

The MAGDOS is also available with an optional Ethernet interface. The stroke frequency, number of strokes, runtime, batch and much more can be controlled via the network interface module. Errors and malfunctions are transmitted from the pump.

The compact structure of the MAGDOS means that it requires a small installation surface. This enables its problem-free integration in smaller compact dosing systems. Depending on the requirements, the pump can be fitted in three different positions: standing, oriented to the left or right and fitted on the wall.

Overview of functions

MAGDOS	LB	LD	LA	LK	LP
Dosing head ventilation (plastic version)	•	•	•	•	•
Graphic display with Backlight (*with multi-language menu)	-	•	•	•*	•*
Password protection	-	•	•	•	•
Supply amount displayed in various units	-	-	-	•	•
Calibration function	-	-	-	•	•
Operating modes	LB	LD	LA	LK	LP
Manual control 0 – 100 %	•	•	•	•	•
External control with pulse increase and reduction	-	•	-	•	•
External control with pulse water meter, PPM u. RERC	-	_1)	-	•	•
Batch dosing with interval and *timer functions	-	-	-	•	•*
External control via standard signal 0/4 – 20 mA	-	-	•	-	•
Inputs and outputs	LB	LD	LA	LK	LP
Release input (external start/stop)	•	•	•	•	•
Level input with early warning and *main alarm	•*	•	•	•	•
Stroke feedback output	-	-	-	•	•
Alarm messages	-	-	-	•	•
Input for flow control	-	-	-	-	•
Diaphragm rupture detection (optional)	-	-	-	-	•
Ethernet interface (optional)	-	-	-	-	•

¹⁾ see online help calculation program:

<http://www.lutz-jesco.com/service/downloads-fachinformationen/online-helfer/berechnungs-assistent-magdos-ld.html>

Technical data


MAGDOS			05	1	2	4	6	10	15
Delivery capacity at max. backpressure	l/h		0.36	0.76	1.9	3.4	6.2	9	13
	ml/stroke		0.05		0.2	0.32	0.57	0.83	0.87
Maximum delivery pressure	bar		16				8	6	3
Delivery capacity at average backpressure	l/h		0.54	1.1	2.3	3.8	6.8	10	15
	ml/stroke		0.08	0.07	0.24	0.35	0.63	0.92	1
Average delivery pressure	bar		8				4	3	1
Nominal stroke frequency	rpm		120	250	160	180		250	
Suction lift for non-gassing media	mWS		5		3		2		
Maximum inflow pressure	mbar		800						
Diameter of diaphragm	mm		24		33		39		
Valve size			DN3*/DN4			DN4			
Voltage supply	LB, LP		100 – 240 V AC, 50/60 Hz						
	LD, LA, LK		210 – 250 or 100 – 125 V AC, 50/60 Hz						
Power consumption	LB, LP	W	10	15	21	27	28	29	26
	LD, LA, LK	W	8	13	19	25		22	
Protection class			IP65 (with covering caps on the connections)						
Insulation class			F						
Materials			PVC, PP, PVDF, 1.4571						
Weight	PVC, PP, PVDF	kg	~3.2						
	1.4571	kg	~4.3						
Approved ambient temperature	PVC	°C	5 – 40						
	PP, PVDF, 1.4571	°C	5 – 45						
Approved media temperature	PVC	°C	35						
	PP, PVDF	°C	60						
	1.4571	°C	80						

* DN3 only for double-ball valve


Delivery characteristic curves

These delivery capacities were determined on the manufacturer's test stands. They apply at 20 °C (68 °F) for water, at 100 % stroke frequency. The delivery capacity depends on the medium (density and viscosity) and temperature. Since these conditions vary at every installation location, you should calibrate the dosing pump.

MAGDOS 05 – 4




MAGDOS 6 – 15



Dimensions


MAGDOS LB with dosing head made of PVC, PP or PVDF

All dimensions in mm




MAGDOS LB with dosing head made of 1.4571/PVDF

All dimensions in mm




MAGDOS LD, LA, LK, LP with dosing head made of PVC, PP or PVDF

All dimensions in mm



MAGDOS LD, LA, LK, LP with dosing head made of 1.4571/PVDF


All dimensions in mm



Connection	Material	Scale	Nominal width	L
Hose clamp connection	PVC, PP, PVDF	4/6 mm	DN4	31 mm
		1/4x3/8"	1/4"	13 mm
		6/9 mm	DN6	34 mm
		6/12 mm	DN6	13 mm
	1.4571/PVDF	4/6 mm	DN4	50 mm
		6/9 mm	DN6	54 mm

Further connection methods for your dosing pumps are available upon request.


MAGDOS standard accessories



Suction lines

Type SL-2 with ceramic reinforcement piece, cable length 3,000 mm, tube length 2,500 mm. Level monitoring and pre-alarm with 2 switching points, switching distance approx. 30 mm. Switching function: Closer on rising level, electrical connection to dosing pump via plug connector M12x1.

Flexible suction line, SA model with foot valve and load part made from ceramic and 2500 mm tube length.



Injection nozzles

To connect the dosing line to the dosing point.

Injection nozzle type S, hose loaded, opening pressure 1.1 bar

Injection nozzle type R, spring loaded, opening pressure 0.1 bar.




Suction and pressure tubes

The stated operating pressure applies at 20 °C in accordance with DIN EN ISO 7751; chemical resistance and correct connection are assumed.



FLOWCON LP 1


- Efficient monitoring of pulsating volume flows
- Compact design, highly robust product
- Easy handling
- Capacity between 0.36 and 15l/h.
- Electric analysis using MAGDOS LP, or performed externally using SPS



PENTABLOC


The PENTABLOC multi-function valve is installed directly on the dosing head of the pump and contains the following features:

- Pressure retaining function, holding pressure 3 bar.
- Pressure relief function, opening pressure of the safety valve 11 bar
- Safety relief function
- Antisiphon function
- Dosing monitoring function




Back-pressure and pressure relief valves

- Back-pressure valves to be mounted in the dosing line.
Adjustable pressure 0.5 – 16 bar.
- Pressure-relief valves to be mounted in the dosing line.
Settable pressure: plastic 0.5 – 16 bar, stainless steel 0.5 – 21 bar



Wall bracket and spacer

- Wall bracket including fixing material for mounting the dosing pump on a wall surface
- Spacer including fastening material for mounting the dosing pump on a water meter



Various cables, plugs and adapters

- Cable for external release of impulse output 0/4 – 20 mA, pulse input A-coded and level monitoring A-coded.
- Cable for alarm (B-coded)
- Ethernet cable for the network connection (D-coded)
- Plug connector for retrofitting existing suction lines or level monitors(A-coded)
- Y-cable: for the parallel use of FLOWCON LP 1 and a leakage detector at the common plug-in connection of the MAGDOS LP (A-coded)
- Adapter, required when using older suction lines with 3.5 mm jack plug (A-coded)